


## Moticam

## 1000

## Standard

## Accessories



Moticam 1000 CMOS camera with C-ring

16mm CCTV lens

28mm, 30mm, 34mm, 35mm  
eyepiece adaptors

USB 2.0 connecting cable  
(permanently attached to camera)

Calibration slide for accurate measurements

Macro viewing tube

Multilanguage Application Software  
(latest version supplied)

Motic USB2.0 PCI capture card



## Specifications

## of

## Moticam

## 1000

Particulars	Moticam 1000
Included Software	Motic Images Plus 2.0 , Multilanguage
Image Device	1/2" CMOS
Lens	16mm
Effective Pixels	1240x1024
Still Image Resolution	1240x1024
Scanning System	Progressive scan mode
Max. Frame Rate	10fps @ 1240x1024 , 30fps @ 640x480
Data Transfer	480MB / second
Minimum Illumination	3 lux
Lens Mount	C-mount (12.5mm)
Shutter	Manual
Video Output	Transmission across Motic software direct into memory of PC
White Balance	Automatic / manual (control by software)
USB Output	Yes
USB Power Supply	5V self-power from computer
Microscope Adaptors	4 different sizes included
USB standard	2.0
Minimum system requirement	P3 1GHZ or higher, HDD 1G unused, RAM 256MB, Display Memory 32MB, Windows2000 & XP